

DGS

Membrane Water Deaeration Unit



Die Application

The Centec DGS Water Deaeration System is a modular water deaeration system utilizing hydrophobic, hollow fibre membrane technology. The use of these highly efficient membrane contactors provides extremely low operating costs, resulting in very low residual oxygen values with low energy and purge gas consumption (CO_2 or N_2). The membranes offer a compact and flexible operation with the ability to increase capacity as water needs increase. The system offers variable capacity from near zero to maximum design flow rate, while maintaining the oxygen specification requirements. The systems can be combined to incorporate other water treatment processing like UV sterilization, heat sterilization, carbon filtration, particle filtration, chilling and carbonation. The systems are CIP compatible and are cleaned as any other section of pipe in the plant.

Technical Data

Capacity	10 - 2000 hl/h
Residual Oxygen	< 0,005 ppm
Temperature	2 - +45°C
Pressure	0,8 bar
Cleaning	CIP up to 85°C
Material	1.4301 / 1.4404 / AISI
Material of the Membrane	Polypropylene
PLC	Siematic S7

- **Expandable by a flash pasteurizer**
for continuous thermal sterilisation
- **Optional Process Visualisation**
Visualize and store continuously the process on the local PLC or at an upper SCADA System
- **Optional In-line oxygen measurement**
for continuous determination and registration of the residual oxygen
- **Optional sealing water recovery**
for the vacuum pump system



- **Hygienic**
in design and fully integrated in the CIP process
- **Flexible**
in operation at variable flow rate
- **Modular**
by the ability to increase capacity
- **Effective**
by using highly efficient membrane contactors





Unsere weltweiten Partner für Vertrieb und Service
Our worldwide partners for sales and service
www.centec.de

Centec Germany (Hauptsitz/Headquarter)
Centec Gesellschaft für Labor-
und Prozessmesstechnik mbH
Wilhelm-Röntgen-Str. 10
D-63477 Maintal / Frankfurt
Tel +49 (0) 6181 1878 0
Fax +49 (0) 6181 1878 50
info@centec.de
www.centec.de

UK representative and distributor:
Protecnica Solutions Limited.
Stalworths, The Street,
Great Tey,
Colchester,
Essex, CO6 1JS,
United Kingdom

www.centec-systems.co.uk
info@centec-systems.co.uk
Tel: +44 (0)1206 211 921 Ext. 22

Centec Czech Republic
Centec automatika spol
s.r.o.
Pekarská 8
CZ-15500 Praha
Tel.: +420 257 084 111
Fax: +420 235 518 701

Centec USA
Centec LLC
P.O. Box 820
Germantown,
WI 53022-0820
Tel.: +1-262 251-8209
Fax: +1-262 251-8376

Centec Brasil
Centec América Latina
Av. das Américas, 500 Bl
13/313
22640-100 Rio de Janeiro,
Tel./Fax:
+55 21 2494 5849

Centec Serbia
Centec Predstavništvo
u Beogradu
Bogdana Zerajica 34
11090 Belgrad, Srbija
Tel./Fax:
+381 11 358 11 24